


Menu - Characteristic stepwise

characteristic stepwise			
Test sequence			
start	manual	load	speed
acceleration with load	NO	start up time	2.0 sec
warm up	NO	warm up time after start	1.0 sec
warm up value	1500 rpm	warm up time	1.0 sec
number of steps	11	aver. count	1
meas. point storing	every load point	stop value	1000 rpm
start value	1500 rpm	meas. time at each step	5.0 sec
ramp time	1.0 sec		
R-measuring	manual		
PS voltage	0.0 V		

Characteristic stepwise



Step characteristic plotting - speed - controlled